



AUSFÜHRUNGEN

Typ	Passend für	Kabellänge m
ZK-GHR12-500-S	CL3-E (IO)	0.5
ZK-GHR3-500-S	CL3-E	0.5
ZK-JST-EHR-6-0.5M-S	SC41, LA42, LGA42, LSA42	0.5
ZK-JST-PHR-6-0.3M	DF45...-A	0.3
ZK-JST-VHR-5N-0.3M	DF45...-A	0.3
ZK-JST-VHR-6N-0.5M-S	SC60	0.5
ZK-MICROUSB	C5, C5-E, CL3-E, CL4-E, PD2-C (USB), PD4-C (USB), PD6-C	1.5
ZK-PD4-C-CAN-4-500-S	PD4-C(B) (CAN), PD2-C(B) (CAN), CL3-E (CAN)	0.5
ZK-USB	PD2-C-IP, PD4-E...-7, SMCI33	1.5
ZK-VHR-3-500	CL4-E-2 (Power)	0.5
ZK-VHR-4-500	CL4-E-2 (Motor)	0.5
ZK-XHP-3-500	CL4-E-1 (Power)	0.5
ZK-XHP-5-500-S	CL4-E (CANopen, RS485)	0.5
ZK-XHP-8-500-S	CL4-E (IO, Encoder)	0.5
ZK-XHP2-500-S	CL3-E (Power)	0.5
ZK-XHP4-300	CL3-E, CL4-E (Motor)	0.3
ZK-ZHR5-90	SMCI36 (Encoder, HALL)	0.09
ZK-ZHR6-500	SMCI36 (IO)	0.5