


SPECIFICATION	
AMPS/PHASE	1.4
RESISTANCE/PHASE (Ohms)@25°C	2.0±15%
INDUCTANCE/PHASE (mH) @1KHz	3.6±20%
SPINDLE PITCH (mm) [in]	5 [0.197]
TRUST (N) [lbf]	100 [17.98]
RESOLUTION (mm/STEP)	0.025
STATIC TRUST (N) [lbf] (NO CURRENT)	30
MAX. SPEED (mm/sec.) AT 48V	250
MAX. SPEED WITH MAX. TRUST (mm/sec.) AT 48V	100
WEIGHT (Kg) [lb]	0.2 [0.44]
TEMPERATURE RISE: MAX.80°C (MOTOR STANDSTILL; FOR 2 PHASE ENERGIZED)	
AMBIENT TEMPERATURE -10°~ 50°C [14°F ~ 122°F]	
INSULATION RESISTANCE 100 MOhm (UNDER NORMAL TEMPERATURE AND HUMIDITY)	
INSULATION CLASS B 130° [266°F]	
DIELECTRIC STRENGTH 500VAC FOR 1 MIN. (BETWEEN THE MOTOR COILS AND THE MOTOR CASE)	
AMBIENT HUMIDITY MAX. 85% (NO CONDENSATION)	

Please regard the application noten at www.nanotec.com for further informations.

Shaft play is adjustable at the motor.

TYPE OF CONNECTION (EXTERN)	MOTOR		
	BIPOLAR	LEADS	WINDING
PIN NO			
1	A —	BRN	A
2	A\ —	ORG	A\
3	B —	RED	B
4	B\ —	YEL	B\



FULL STEP 2 PHASE-Ex., WHEN FACING MOUNTING END (X)

STEP	A	B	A\	B\	CW
1	+	+	-	-	
2	-	+	+	-	
3	-	-	+	+	
4	+	-	-	+	

REV	DESCRIPTION	DATE	APVD
1	NEW VALUES AND NOTE	06.05.10	J.W.



L4118S1404-T5x5

SCALE	APVD	S.H.	DATE
FREE	CHKD		04.06.09
X ±0.5	DRN	J.W.	04.06.09
1PL ±0.2	SIGNATURE		DATE
2PL ±0.1			
ANGLE ±30'			

LINEAR ACTUATOR

DWG.NO
L4118S1404-T5x5